



SPERIAN

EYEWASH / EMERGENCY SHOWERS

Eyewash Stations	80
Eyewash Solution	81
Emergency Showers	81



FEND-ALL PURE FLOW 1000® EYEWASH STATION



- Sturdy, hi-vis container with fluid reservoir and soft “ribbon” nozzles
- Delivers 0.4 gpm over 15 minutes flushing period as required by ANSI Z358.1-2004 as a primary device
- Includes one set of cartridges

FDA 320010000000 English
 FDA 320010000022 French Canadian
 FDA 320010500000 English refill cartridges



PORTA STREAM® II EYEWASH STATION



- Simple, highly visible operating instructions
- Easy to use, easy to install
- Large 6 litre capacity permits thorough flushing by providing 0.4 gpm over the entire 15 minute flushing period required by ANSI Z358.1-2004

FDA 320002000000



FEND-ALL PORTA STREAM® III EYEWASH STATION



- Self-contained, sturdy, large 16 gal. capacity container
- Moulded handle, nozzle strap and “full-flow” nozzles
- Provides 0.4 gpm over full 15 minutes flushing period as required by ANSI Z358.1-2004 as a primary device
- Accommodates optional flushing solutions such as Eyesaline®, or Fend-All® water preservative

FDA 320002300000 English
 FDA 320002300022 French
 FDA 320003100000 English, freeze protected



ON-SITE® GRAVITY FED EYEWASH STATION



- Polycarbonate tank and pedestal with hinged pull-down eyewash tray and wall mount brackets
- 7 gal. capacity provides 15 minutes of flushing at 0.4 gpm
- Complies with ANSI Z358.1-2004 standards

BDY 519921



GRAVITY FED EYEWASH STATION



- Hi-vis yellow polyethylene tank with two carrying handles
- Installation, operation and maintenance instructions on front
- Pull down tray stays in fixed, open position during activation
- Dual stream of water at 0.4 gpm (1.5 lpm)
- EW fill level - 15 minute, 14 gal.

ENC 01104050



EMERGENCY EYEWASH STATION



- Includes:
 (1) single panel (NOR EA3833)
 (1) 32 oz. bottle (NOR EA1507BISO)

NOR EA3828



FULL EYEWASH STATION



- Includes:
 (1) single panel (NOR EA3837)
 (1) full 32 oz. squeeze bottle (NOR EA1507BISO)

NOR EA3840



EMPTY EYEWASH STATION



- Includes:
 (1) single panel
 (1) 32 oz. empty bottle with spill spout and eye cup

NOR EA3825
 NOR EA3835 Empty eyewash bottle



PORTABLE EYEWASH STATION



- Sturdy, white, pre-moulded, high impact plastic board
- Comes with an empty eyewash bottle, eye cup and a mirror

WAS F4560701 Single 32 oz.
 WAS F4565701 Dual 32 oz.



EYEWASH BOTTLE



- Soft, flexible polyethylene
- Built-in eye cup and snap-on lid
- Drainage tube and air vent valve prevent the used solution from entering back into the bottle
- Comes empty with eye cup

WAS F4570301 32 oz.
 WAS F4573301 16 oz.



FEND-ALL PORTA STREAM® I AND II DUST COVER



- For use with Porta Stream® I and II to protect the eyewash basin from dirt, dust and debris
- Attached to the eyewash pull strap
- Cover and pull strap are removed in one motion

FDA 320005170000



STERILE ISOTONIC SOLUTION



- Sterile 0.9%
- NOR E1507AISO 500 mL
 NOR E1507BISO 32 oz.
 NOR E1507CISO 4 L



FEND-ALL PURE FLOW 1000® HIGH HUMIDITY CARTRIDGES



- Designed for units located in high humidity moisture levels of 80% and higher
- Set of two

FDA 320010520000



NEUTRALIZING SOLUTION



- A sterile solution of Ph7
- Helps in neutralizing acid and alkaline chemical splashes in the eyes and on the body

WAS F4505189 4 L



SALINE CONCENTRATE



- Specifically formulated to be mixed with potable water
- Mixes quickly with water to provide a preserve, buffered, saline solution
- Ten parts water to one part concentrate mixing ratio

FDA 320005130000



SHOWER / EYEWASH STATION



- Includes 10" showerhead and 10" eyewash bowl
- Made of yellow impact resistant plastic
- Showerhead exceeds minimum water flow (20 gpm)
- Hinged stainless steel dust cover keeps out contaminants and debris from eyewash area and opens when the handle is activated
- Chrome plated circular spray ring designed with a wider spray pattern for full face spray
- ANSI Z358.1-1998 compliant
- Many options available, call for details

BDY S19310



HYDROSEP EYE WASH ADDITIVE



- Each bottle treats up to five to 20 gallons for 90 days

ENC 01110764EA



COMBINATION SHOWER AND EYEWASH



- ABS plastic showerhead with integral flow control
- 304 stainless steel bowl with eyewash heads containing integral flow controls
- 1-1/4" hot dip galvanized pipe
- Foot treadle included
- Call for other options

HWS 8300



BUFFERED SALINE ISOTONIC SOLUTION



- Pre-mixed, ready-to-use, sterile buffered saline isotonic solution
- Designed for the cleansing of irritated eyes caused by exposure to foreign materials, air pollutants, pollen, over-chlorinated water and non-toxic chemical splashes
- Medicinal ingredient, 1.9% boric acid

WAS F4510189

